

Poly (Box) Trucks (see page 19 for Poly-Bins)



Bayhead Poly-Trucks are available in 19 sizes, molded in heavy-duty polyethylene. Molded vertical ribs in medium sizes provide superior rigidity & strength. Optional lids for many sizes help protect contents. Most trucks are available in a variety of colors for no extra cost.

Molded polyethylene bodies are secured to an all-welded angle-iron dolly by bolting through the bodies. 5" casters are welded in a corner pattern for sizes 10 through 80 bushel. Sizes 4 through 9 bushel use 3" casters. Note: Standard units are not leakproof unless requested when ordering.

Model Number	Bushel Cap.	Gallon Cap.	OD Top LxWxD	ID Top LxW	ID Bottom LxW	Overall Height	Pound Cap.	Cart Weight	Standard Lid	Lid Weight	Janitorial Lid
UT-4	4	30	32.75" x 21.25" x 15.75"	29.25" x 17.5"	24.75" x 15"	19.75"	400 lb.	24 lb.	PBL-4	9 lb.	N/A
UT-6	6	41	32.25" x 23.25" x 20"	29" x 20"	23.5" x 16"	24"	400 lb.	25 lb.	PBL-6	9 lb.	N/A
UT-7	7	51	37" x 24.5" x 19.75"	33.5" x 21.5"	28.5" x 17.25"	23.75"	400 lb.	38 lb.	PBL-7	10 lb.	N/A
UT-8	8	57	36.25" x 24.25" x 23"	32.25" x 20.5"	28.5" x 17"	27"	400 lb.	35 lb.	PBL-8	10 lb.	N/A
UT-9	9	66	41.5" x 29.5" x 19"	37" x 25"	33" x 21"	23"	600 lb.	42 lb.	N/A	(Very low truck height)	
UT-10	10	73	38.25" x 29.25" x 24.5"	34.25" x 25"	28" x 19.5"	31"	600 lb.	41 lb.	PBL-10	11 lb.	BLN-10
UT-12	12	84	38" x 28.25" x 27.75"	33.75" x 23.5"	30" x 20.25"	34.25"	600 lb.	45 lb.	PBL-12	11 lb.	BLN-12
UT-14	14	115	43.75" x 31.75" x 28.5"	39" x 27.5"	35.5" x 23.5"	35"	600 lb.	53 lb.	PBL-14	15 lb.	BLN-14
UT-15	15	120	58.5" x 29" x 25.5"	53.25" x 24"	48.5" x 19"	32"	800 lb.	61 lb.	N/A	(Long-sided truck)	
UT-16	16	125	45" x 31" x 29.5"	40.5" x 27"	36" x 23"	36"	800 lb.	57 lb.	PBL-16	15 lb.	BLN-16
UT-17	17	133	46" x 24.5" x 36"	42.5" x 22"	40" x 19.5"	43"	800 lb.	62 lb.	N/A	(Truck tall and narrow)	
UT-18	18	145	46.25" x 34" x 31"	42.25" x 29.5"	38" x 25.5"	37.75"	800 lb.	63 lb.	PBL-18	17 lb.	BLN-18
UT-20	20	151	46" x 34" x 32.5"	41.5" x 29.75"	37" x 25"	39"	800 lb.	68 lb.	PBL-20	17 lb.	BLN-20
UT-22	22	185	62" x 32" x 28"	58" x 28.5"	54" x 25.5"	33"	1000 lb.	90 lb.	N/A	(3" recess on bottom)	
UT-25	2	215	63.25" x 35.5" x 33.25"	58" x 30.5"	53" x 24"	39.75"	1000 lb.	95 lb.	N/A	N/A	N/A
UT-30*	30	315	71" x 43" x 34"	66" x 38"	58" x 31"	42"	1000 lb.	145 lb.	N/A	(Notch: 59" x 12")	
UT-40	40	320	71" x 47.5" x 30"	66" x 43"	58" x 36"	36.75"	1000 lb.	145 lb.	N/A	N/A	N/A
UT-50	50	445	84" x 50" x 30"	80" x 45.5"	76" x 42"	36.75"	1000 lb.	180 lb.	N/A	N/A	N/A
UT-80	80	750	102.5" x 46" x 44"	99.5" x 43"	95" x 40"	50.75"	1000 lb.	253 lb.	N/A	N/A	N/A

*Note: UT-30 has a notch molded into one long side. See picture on opposite page.



Note: Six casters standard on UT-80: four swivel and two rigid.

Not the right size?
Give us a call - we
can make a truck to
your specifications!