

Self-Dumping Hoppers - Available in five sizes up to 3.0 cubic yard



SD-1.1-C upright



SD-1.1-C dumping

Our molded polyethylene Self-Dumping Hoppers are designed to allow safe and easy handling and dumping of heavy loads. Bins dump up to 40 degrees below horizontal with a simple pull of the handle. Made to work with a forklift, but optional 6" heavy-duty casters allow for easy manual maneuverability. Please note: bottom frame should always be secured to the fork lift prior to dumping.

Model Number	Cu. Yd. Capacity	Pound Capacity	Cu. Ft. Capacity	Gallon Capacity	Overall Dimension*	Height w/ Casters	Weight	Weight w/ Casters	Lid Number
SD-5/8	5/8	750 lb.	16	123	59" x 26" x 42"	49"	175 lb.	220 lb.	5/8-LID
SD-1.1	1.1	1000 lb.	29	220	71" x 31" x 46"	53.5"	210 lb.	258 lb.	1.1-LID
SD-1.7	1.7	1200 lb.	50	366	80" x 40" x 55"	62.5"	300 lb.	354 lb.	1.7-LID
SD-2.2	2.2	1500 lb.	59	441	80" x 51" x 55"	62.5"	331 lb.	386 lb.	2.2-LID
SD-3.0	3.0	1700 lb.	78	585	90" x 56" x 63"	70.5"	400 lb.	460 lb.	3.0-LID

*Note - includes metal framework.

Check us out against steel hoppers-

Plastic hoppers are:

- Lighter
- Quieter
- Safer (body has no sharp edges)
- Easier to handle
- Body won't rust or corrode
- Easily Cleaned
- All-welded steel frame
- Variety of body colors

Available Options:

- Hinged lids
- 6" casters
- Side support bars
- Stenciling
- Drains



SD-1.7-C