

COMPACT CENTRIFUGES

6 x 50 ml

Z206-A

Up to 12 x 15 ml sample tubes (also conical) can be used in the Z206-A. Adapters are available for smaller tube dimensions and blood collection systems. For larger volumes, a fixed-angle rotor for 6 x 50 ml tubes (conical and round bottom) is also available.



Information about the control panel can be found on page 8.

TECHNICAL SPECIFICATIONS

MAX. SPEED	6,000 rpm
MAX. RCF	4,467 xg
MAX. VOLUME	6 x 50 ml
SPEED RANGE	200–6,000 rpm in 50 rpm increments / 10 rcf increments
RUNNING TIME	59 min 50 s / 10 s increments or 99 h 59 min / 1 min increments
DIMENSIONS (W X H X D)	11 in x 10 in x 15.5 in / 28 cm x 26 cm x 37 cm
WEIGHT	26.5 lbs / 12 kg

ORDER NUMBERS

Z206-A, 120 V / 50 – 60 Hz / 100 W

Z206-A-E, 230 V / 50 – 60 Hz / 100 W

Main rotor



Max. volume: 12 x 15 ml
Round bottom and conical
Order number: Z206-1215



Max. volume: 6 x 50 ml
Round bottom and conical
Order number: Z206-0650

ROTORS

MAX. VOLUME	MAX. SPEED	RCF VALUE	ORDER NUMBERS	ANGLE
6 x 50 ml	6,000 rpm	4,427 xg	Z206-0650	40°
12 x 15 ml	6,000 rpm	4,427 xg	Z206-1215	32°
18 x 1.5/2.0 ml	6,000 rpm	2,938 xg	Z206-1820	45°
6 x 5.0 ml	4,000 rpm	1,896 xg	Z206-0605	0–90°
4 x 4.0–7.0 ml	6,000 rpm	4,467 xg	Z206-0457	0–77°

The respective max. capacities of the rotors are shown in the tables. Naturally, adapters are available for smaller volumes. Detailed information can be found in our individual brochures on our homepage:

www.HermleUSA.com/download

If you cannot find the required adapter, we will gladly make a custom adapter for you.