

ROTORS

MAX. VOLUME	MAX. SPEED	RCF VALUE	ORDER NUMBER	ANGLE
4 x 145 ml	4,500 rpm	3,350 xg	Z306-100	0 – 90°
4 x 100 ml	4,000 rpm	2,611 xg	Z326-100H	0 – 90°
30 x 15 ml	4,500 rpm	2,830 xg	Z326-3015	35°
6 x 50 ml	6,000 rpm	4,427 xg	Z326-0650-LS	40°
12 x 15 ml	6,000 rpm	4,427 xg	Z326-1215	32°
12 x 5 ml	14,000 rpm	18,624 xg	Z326-1205	45°
30 x 1.5/2.0 ml	12,000 rpm	15,131 xg	Z326-3020H	45°
24 x 1.5/2.0 ml	14,000 rpm	18,624 xg	Z326-2420	45°
24 x 1.5/2.0 ml*	14,000 rpm	18,624 xg	Z326-2420H	45°
2 x 3 Microplates	4,500 rpm	2,716 xg	Z326-02MP	0 – 90°

* hermetically sealed

EXAMPLE ROTORS

Main rotor



Max. volume: 4 x 145 ml
Order number: Z306-100



Max. volume: 2 x 3 Microplates
Order number: Z326-02MP



Max. volume: 6 x 50 ml
Order number: Z326-0650-LS



Max. volume: 12 x 15 ml
Order number: Z326-1215



Max. volume: 30 x 1.5/2.0 ml
Order number: Z326-3020H



Max. volume: 12 x 5 ml
Order number: Z326-1205

The respective max. capacities of the rotors are shown in the tables. Naturally, adapters are available for smaller volumes. Detailed information can be found in our individual brochures on our homepage:

www.HermleUSA.com/download

If you cannot find the required adapter, we will gladly make a custom adapter for you.