

## ROTORS

MAX. VOLUME	MAX. SPEED	RCF VALUE	ORDER NUMBER	ANGLE
4 x 750 ml*	4,000/4,500 rpm	3,434/4,346 xg	Z446-750	0 – 90°
4 x 500 ml	8,000 rpm	10,374 xg	Z446-04500	24°
6 x 250 ml	8,000 rpm	10,016 xg	Z366-06250	28°
6 x 85 ml	11,000/13,000 rpm	15,555/21,726 xg	Z326-0685	38°
10 x 50 ml conical	10,000/10,500 rpm	14,532/16,022 xg	Z326-1050	38°
4 x 85 ml	15,000/16,000 rpm	23,140/26,328 xg	Z326-0485	30°
6 x 50 ml	13,000 rpm	15,869 xg	Z326-0650-HS	26°
20 x 10 ml	12,000 rpm	15,775 xg	Z326-2010	30°
44 x 1.5/2.0 ml	16,000 rpm	24,038/24,325 xg	Z326-4420	32°/55°
30 x 1.5/2.0 ml	15,000 rpm	23,643 xg	Z326-3020H	45°
24 x 1.5/2.0 ml	16,000 rpm	24,325 xg	Z326-2420	45°
24 x 1.5/2.0 ml*	16,000 rpm	24,325 xg	Z326-2420H	45°
2 x 3 Microplates	4,500 rpm	2,716 xg	Z326-02MP	0 – 90°
4 x 8-PCR strips	15,000 rpm	15,343 xg	Z326-3202	45°

\* hermetically sealed

## EXAMPLE ROTORS

Main rotor



Max. volume: 4 x 750 ml  
Order number: Z446-750  
hermetically sealed



Max. volume: 4 x 500 ml  
Order number: Z446-04500



Max. volume: 2 x 3 Microplates  
Order number: Z326-02MP



Max. volume: 6 x 85 ml  
Order number: Z326-0685



Max. volume: 10 x 50 ml conical  
Order number: Z326-1050



Max. volume: 24 x 1.5/2.0 ml  
Order number: Z326-2420H  
Hermetically sealed

The respective max. capacities of the rotors are shown in the tables. Naturally, adapters are available for smaller volumes. Detailed information can be found in our individual brochures on our homepage: [www.HermleUSA.com/download](http://www.HermleUSA.com/download)  
If you cannot find the required adapter, we will gladly make a custom adapter for you.