

# Consumables (continued)

## Universal Conventional Liners (rear-loading)

### 10' (3.05 m) Gun Lengths

<b>L3A-10</b>	for 0.035" - 0.045" wire
<b>L4A-10</b>	for 0.045" - 1/16" wire

### 15' (4.57 m) Gun Lengths

<b>L1A-15</b>	for 0.023" - 0.030" wire
<b>L2A-15</b>	for 0.030" - 0.035" wire
<b>L3A-15</b>	for 0.035" - 0.045" wire*
<b>L4A-15</b>	for 0.045" - 1/16" wire**
<b>L6A-15</b>	for 5/64" wire
<b>L7A-15</b>	for 3/32" wire
<b>L8A-15</b>	for 7/64" - 1/8" wire

### 25' (7.62 m) Gun Lengths

<b>L1A-25</b>	for 0.023" - 0.030" wire
<b>L2A-25</b>	for 0.030" - 0.035" wire
<b>L3A-25</b>	for 0.035" - 0.045" wire*
<b>L4A-25</b>	for 0.045" - 1/16" wire**
<b>L6A-25</b>	for 5/64" wire
<b>L7A-25</b>	for 3/32" wire
<b>L8A-25</b>	for 7/64" - 1/8" wire

\*Standard Liner for 0.035" & 0.045" Guns

\*\*Standard Liner for 1/16" Guns

See Universal Conventional Liner Spec Sheet (SP-L) for more information

## Conventional Liners for Aluminum Wire (rear-loading)

### 10' (3.05 m) Gun Lengths

<b>415-45-02</b>	for 0.035" - 3/64" wire Polymer Liner
<b>415-116-22</b>	for 3/64" - 1/16" wire Polymer Liner

### 15' (4.57 m) Gun Lengths

<b>415-45-03</b>	for 0.035" - 3/64" wire Polymer Liner
<b>415-35-2</b>	for 0.035" - 0.045" wire Steel Wrapped Nylon
<b>415-116-2</b>	for 0.045" - 1/16" wire Steel Wrapped Nylon
<b>415-116-23</b>	for 3/64" - 1/16" wire Polymer Liner

### 25' (7.62 m) Gun Lengths

<b>415-45-04</b>	for 0.035" - 0.045" wire Steel Wrapped Nylon
------------------	---

## Power Pins

(available through configurator)

### Bernard™

<b>1880259B</b>	Quick Disconnect Kit
<b>2200140</b>	Power Pin (Includes O-Rings)

### Euro

<b>1880259E</b>	Power Pin Kit
<b>5060T</b>	Euro Block Assembly
<b>4816</b>	Adaptor Nut

### Lincoln®

<b>1880259L</b>	Power Pin Kit
<b>214-2-1</b>	Power Pin

### AutoLength Pin

<b>425-820E</b>	for 0.030"-0.045"
<b>428-920E</b>	for 0.052"-3/32"

### AutoLength Pin

<b>214-87</b>	for 0.030"-0.045"
<b>214-97</b>	for 0.052"-3/32"

### Miller®

<b>1880259M</b>	Power Pin Kit
<b>2200137</b>	Power Pin (Includes O-Rings)

### OXO™

<b>1880259X</b>	Power Pin Kit
<b>427-12</b>	Power Pin

### AutoLength Pin

<b>214-81</b>	for 0.030"-0.045"
<b>214-91</b>	for 0.052"-3/32"
<b>214-9</b>	for 7/64" - 1/8"

### Tweco® #4

<b>1880259T4</b>	Power Pin Kit
<b>214</b>	Power Pin (Includes O-Rings)

### Tweco® #5

<b>1880259T5</b>	Power Pin Kit
<b>214-12</b>	Power Pin (Includes O-Rings)

### AutoLength Pin

<b>214-80</b>	for 0.030"-0.045"
<b>214-90</b>	for 0.052"-3/32"

### AutoLength Pin

<b>214-812</b>	for 0.030"-0.045"
<b>214-912</b>	for 0.052"-3/32"

See Universal Power Pin Spec Sheet (SP-PPK) for more information