



**PowerSTAR**

## 712 Series AC Three Phase Inverter Duty

POWERSTAR

Model #	Horsepower	Speed (RPM)	Torque (in lbs)	Ratio	OHL	Voltage	Amps	Shipping Wt.
027-712G0010	1/20	167	10	10	145	230	0.3	7
027-712G0015	1/20	111	15	15.1	166	230	0.3	7
027-712G0020	1/20	84	20	20.1	182	230	0.3	7
027-712G0030	1/20	56	30	30.3	206	230	0.3	7
027-712G0040	1/20	42	40	40.4	226	230	0.3	7
027-712G0050	1/20	34	50	49.8	241	230	0.3	7
027-712G0060	1/20	28	60	59.8	254	230	0.3	7
027-712G0080	1/20	21	80	80.3	268	230	0.3	7
027-712G0100	1/20	17	100	100.4	285	230	0.3	7
027-712G0120	1/20	14	120	120.4	299	230	0.3	7
027-712G0150	1/20	11	150	149.9	315	230	0.3	7
027-712G0180	1/20	9.3	180	180.7	328	230	0.3	7
027-712G0200	1/20	8.4	200	200.7	333	230	0.3	7
027-712G0240	1/20	7	240	240.9	344	230	0.3	7



**PowerSTAR**

## 720 Series AC Three Phase Inverter Duty

Model #	Horsepower	Speed (RPM)	Torque (in lbs)	Ratio	OHL	Voltage	Amps	Shipping Wt.
027-720G0010	1/8	167.8	35	10	270	230	0.63	16
027-720G0015	1/8	112	55	15	305	230	0.63	16
027-720G0020	1/8	83.9	73	20	330	230	0.63	16
027-720G0030	1/8	55.9	105	30	370	230	0.63	16
027-720G0040	1/8	41.9	145	40	400	230	0.63	16
027-720G0050	1/8	33.5	180	50.1	430	230	0.63	16
027-720G0060	1/8	27.9	220	60.1	455	230	0.63	16
027-720G0080	1/8	20.9	295	80.1	490	230	0.63	16
027-720G0100	1/8	16.6	365	100.2	525	230	0.63	16
027-720G0120	1/8	14	440	120.2	550	230	0.63	16
027-720G0150	1/15	11	295	150.3	635	230	0.39	16
027-720G0180	1/15	9.3	355	180.3	670	230	0.39	16
027-720G0240	1/15	7	470	240.4	725	230	0.39	16