



Actual

Catalog Number: 13-240
Product ID: 7TCA008010R0044
UPC Number: 78378613240
EAN Number: 05414363201311
Status: Active

Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 142mm (5.59 Inches), Width of 2.5mm (0.10 Inches), Thickness of 1.2mm (0.05 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds)

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Brand Name	T&B Electricians' Supplies
Type	Cable Tie
Application	For Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications
Width	0.10 Inches/2.54mm
Length	5.59 Inches/142mm
Thickness	0.05 Inches/1.2mm
Bundle Diameter	Max 1.25 Inches/32 mm
Material	Polyamide/Nylon 6.6
Color	Natural
Lock Mechanism	Double Locking Head
Tensile Strength	18 Pounds/80 Newtons

Packaging

Inner Quantity	50
Inner Dimensions (inches)	9x5x.5
Outer Quantity	1000
Outer Dimensions (inches)	10x6.7x5.2
Weight Uom	0.63 lbs. per 1000

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com