

Catalog Number: 2T
Product ID: 7TAH006040R0016
UPC Number: 78378603679
Status: Active
Replacement Catalog: 9H

Split Bolt Connector - Wire Range: Main 10 Stranded - 12 Solid, Tap 10 Stranded - 14 Solid, Metric 2.5 - 4 millimeters squared, UL Listed 2 #10 - 2 #12 AWG Copper or #10 Run and #12 - 14 Tap

North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Color-Keyed
Type	Split-Bolt Connector
Standard	UL E9809

European Specifications (ETIM)

ETIM	EC000491 Earth terminal clamp
Suitable for	Round conductor
Material	Copper

Packaging

Inner Quantity	100
Inner Dimensions (inches)	4.09x3.03x2.72
Outer Quantity	1000
Outer Dimensions (inches)	14.81x6.5x4.38
Weight Uom	2.5 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com