

Catalog Number: HL 10-48-HM
Product ID: 7TAA267120R0000
UPC Number: 78378673136
Status: Active

Copper Compression Lug, Bolt 1/2 inch, One Hole Pad, #10 Stranded, Peep Hole, Tin-Plated, 1.19 inch Long, Pad is .750 inch wide (pancake shaped) and is marked for 12-10.

North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Brand Name	Homac
Type	Compression Lug
Special Features	Peep Hole, Tin-Plated, Marked 12-10
Cable Size	12-10
Stud Size	1/2 inch
Number Of Holes	1
Material	Copper
Connection	Compression/Crimp
Size	1.19 inch Long, .750 inch wide

European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
With sight-hole	Y
Material	Copper
Surface protection	Tinned
Number of fixing holes	1

Packaging

Outer Quantity	500
Outer Dimensions (inches)	6.25x4.5x3.5
Weight Uom	1 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com