



Representative

Catalog Number: PAA1293P
Product ID: 7TAA267200R0008
UPC Number: 78378685245
Status: Active

Parallel Groove Clamp, Hex Head Bolt, Contax Filled, Tin Plated, Main 4/0 - 2 ACSR 4/0 - 2 SOL Aluminum, TAP 4/0 - 2 ACSR 4/0 - 2 SOL Aluminum

North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Blackburn
Type	Parallel-Groove Clamp
Special Features	High-Strength, Heat-Treated Cast Aluminum Alloy provides Secure Connections. Galvanized Steel Carriage Bolt, Nut and Lockwasher included. Dual-Rated for use on Aluminum, ACSR and Copper Conductors.
Application	Securing Conductors
Size	Bolt Hex-Head 3/4 inch, Bolt Size 1/2 inch, Height 2-1/4 X Length 2 X Width 2 inch
Connection	Bolted
Conductor Range	Main 4/0 - 2 ACSR 4/0 - 2 SOL Aluminum, TAP 4/0 - 2 ACSR 4/0 - 2 SOL Aluminum
Number Of Conductors	2
Material	Aluminum
Insulation	None
Mounting	None
Environmental Conditions	All Seasons / Conditions

Packaging

Inner Quantity	25
Inner Dimensions (inches)	7x6.43x5.37
Outer Quantity	150
Outer Dimensions (inches)	19.25x11.31x8
Weight Uom	38.5 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com