



Representative

Catalog Number: PAE9939-7
Product ID: 7TAA267200R0059
UPC Number: 78378685535
Status: Active

Parallel Groove Clamp, Aluminum Hardware, Conductor Range Main 1000 kcmil - 397.5 AC-SR 336.4 - 2/0 AR, TAP 397.5 ACSR - 3.0 Stranded 2/0 - 6 AR

North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Blackburn
Type	Parallel-Groove Clamp
Special Features	Galvanized Steel Hardware Provides High Strength for Heavy-Duty Applications. Install with Live Line Tools you Already Have. Dual-Rated for Aluminum-to-Copper Connections.
Application	Securing Conductors
Size	Height 2-13/16 X Length 3-1/2 X Width 3-7/64 inch, Bolt 1/2 inch
Connection	Bolted
Conductor Range	Main 1000 kcmil - 397.5 ACSR 336.4 - 2/0 AR, TAP 397.5 ACSR - 3.0 Stranded 2/0 - 6 AR
Number Of Conductors	2
Material	Aluminum
Insulation	None
Mounting	None
Environmental Conditions	All Seasons / Conditions

Packaging

Inner Quantity	5
Inner Dimensions (inches)	10.5x7.25x3.31
Outer Quantity	25
Outer Dimensions (inches)	19.38x11x7.63
Weight Uom	9.49 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com