


## Pressed steel compact castors with top plate

75–350 kg



- Bracket:** LPA, LKPA, LE/B, L/B, LK/BK series
- pressed steel, zinc-plated, blue-passivated, Cr6-free
  - double ball bearing in the swivel head
  - minimum swivel head play and smooth rolling characteristic and increased service life due to the special dynamic Blickle riveting process
  - bracket overview:
    - series LPA page 86
    - series LKPA page 86
    - series LE/B page 90
    - series L/B page 91
    - series LK/BK page 92
  - brakes: page 112–113



- Wheel:** POEV series
- tyre: high-quality elastic solid rubber “Blickle EasyRoll” in smooth rolling quality, hardness 65 Shore A, colour black
  - wheel centre: high-quality nylon 6, impact resistant, colour black
  - detailed description: page 63, 212



- Wheel:** VSTH series
- tread: high-quality polyurethane elastomer Blickle Extrathane®, hardness 92 Shore A, colour light brown, non-marking, non-staining
  - wheel centre: steel
  - detailed description: page 66, 286



- Wheel:** POA series
- high-quality nylon 6, impact resistant, hardness 70 Shore D, colour black
  - detailed description: page 61, 143



- Wheel:** PO series
- high-quality nylon 6, impact resistant, hardness 70 Shore D, colour natural white
  - detailed description: page 69, 343



- Wheel:** GSPO series
- high-quality cast nylon, reaction-injected, impact resistant, hardness 80 Shore D, colour natural beige
  - detailed description: page 70, 368

Swivel castors	Fixed castors	Swivel castors with “Radstop” brake	Wheel Ø [mm]	Wheel width [mm]	Load capacity at 3 km/h [kg]	Bearing type	Total height [mm]	Plate size [mm]	Bolt hole spacing [mm]	Bolt hole Ø [mm]	Offset swivel castor [mm]
<b>LPA series</b>											
LPA-POA 35G		LPA-POA 35G-RA	35	25	75	plain bore	52	60 x 60	38 x 38 / 48 x 48	6.2	15
LPA-VSTH 35K		LPA-VSTH 35K-RA	35	27	100	ball bearing	52	60 x 60	38 x 38 / 48 x 48	6.2	15
LPA-GSPO 35K		LPA-GSPO 35K-RA	35	28	100 *	ball bearing	52	60 x 60	38 x 38 / 48 x 48	6.2	15
<b>LKPA series</b>											
LKPA-POA 52G		LKPA-POA 52G-RA	50	29	120	plain bore	73	90 x 66	75 x 45 / 61 x 51	8.5	29
LKPA-GSPO 50K		LKPA-GSPO 50K-RA	50	32	150 *	ball bearing	73	90 x 66	75 x 45 / 61 x 51	8.5	29
LKPA-VSTH 50K		LKPA-VSTH 50K-RA	50	33	150	ball bearing	73	90 x 66	75 x 45 / 61 x 51	8.5	29
<b>LE series</b>											
LE-PO 60G	B-PO 60G	LE-PO 60G-RA	60	29	150	plain bore	80	100 x 85	80 x 60	9	35
LE-PO 60KF	B-PO 60KF	LE-PO 60KF-RA	60	32	150	ball bearing (C)	80	100 x 85	80 x 60	9	35
LE-POEV 60KF	B-POEV 60KF	LE-POEV 60KF-RA	60	34	120	ball bearing (CC)	80	100 x 85	80 x 60	9	35
<b>L series</b>											
L-GSPO 60K	B-GSPO 60K	L-GSPO 60K-RA	60	32	250 *	ball bearing	80	100 x 85	80 x 60	9	35
L-VSTH 60K	B-VSTH 60K	L-VSTH 60K-RA	60	35	200	ball bearing	80	100 x 85	80 x 60	9	35
<b>LK series</b>											
LK-GSPO 65K	BK-GSPO 65K		65	40	350 *	ball bearing	90	100 x 85	80 x 60	9	40
LK-VSTH 65K	BK-VSTH 65K		65	40	250	ball bearing	90	100 x 85	80 x 60	9	40

\* Test in compliance with DIN 12530 with extended breaks to avoid thermal overloading