

Part Number	Product Name	Page	Unit	W (L)	H	D	Product Weight	
HH004-0412	Hanger - Glass and Laminate - Quartz Beige Powder-Coated Steel	11	IN	10.00	4.62	0.56	LB	0.5
			CM	25.4	11.7	1.4	KG	0.2
HP-010	Hairnet Dispenser - Bulk - Clear PETG Plastic	71	IN	4.64	7.88	3.68	LB	0.7
			CM	11.8	20.0	9.3	KG	0.3
KS010-0412	Floor Stand - All Steel - Quartz Beige Powder-Coated Steel	24, 25	IN	18.00	36.06	18.00	LB	16.0
			CM	45.7	91.6	45.7	KG	7.3
KS101-0029*	Hand Sanitizer Floor Stand - Bay Gray Steel Back Plate, Column, and Base	34	IN	18.00	54.73	18.00	LB	16.0
			CM	45.7	139.0	45.7	KG	7.3
KS102-0029*	Hand Sanitizer Floor Stand - Bay Gray Steel Back Plate, Column, and Base - Quartz Beige ABS Plastic Drip Tray	Not Pictured	IN	18.00	54.73	18.00	LB	16.3
			CM	45.7	139.0	45.7	KG	7.4
KS122-0529	Infection Prevention Station - Bay Gray Powder-Coated Aluminum	Not Pictured	IN	7.21	15.11	4.29	LB	2.0
			CM	18.3	38.4	10.9	KG	0.9
KS123-0529	Infection Prevention Station Accessory for Hand Sanitizer Floor Stand - Bay Gray Powder-Coated Aluminum with Semi-Permanent VHB Tape	Not Pictured	IN	7.21	15.11	4.29	LB	2.0
			CM	18.3	38.4	10.9	KG	0.9
KS201-0029*	Floor Stand - Bay Gray Powder-Coated Steel Mounting Plate, Column, and Base	25	IN	18.00	36.73	18.00	LB	15.3
			CM	45.7	93.3	45.7	KG	6.9
LB100-0212	Safety Eyewear Dispenser - Divided - Quartz Beige ABS Plastic	70	IN	20.75	15.75	7.13	LB	8.3
			CM	52.7	40.0	18.1	KG	3.8
LD-007	Protection System - Quartz Beige ABS Plastic (Aluminum Version PS021-0512)	9, 12	IN	16.63	25.13	4.62	LB	4.5
			CM	42.2	63.8	11.7	KG	2.0
LD-037	Protection System - Quartz Beige ABS Plastic (Aluminum Version PS022-0512)	9, 12	IN	23.50	20.80	4.75	LB	5.6
			CM	59.7	52.8	12.1	KG	2.5
LD-064	Protection System - 4" Deep - Quartz Beige ABS Plastic	12, 15	IN	16.77	25.63	4.00	LB	3.7
			CM	42.5	65.1	10.2	KG	1.7
LD-070	Protection System - Quartz Beige ABS Plastic	9, 12	IN	20.05	25.25	4.75	LB	4.6
			CM	50.9	64.1	12.1	KG	2.1
LP-004	Protection System - Surgical - Quartz Beige ABS Plastic & Clear PETG Plastic (Aluminum Version PS023-0512)	Not Pictured	IN	22.15	19.68	4.88	LB	4.8
			CM	56.3	50.0	12.4	KG	2.2
MB-450	Hanger - Metal Bracketed Door - Quartz Beige Powder-Coated Steel	11	IN	26.14	29.49	2.92	LB	2.5
			CM	66.4	74.9	7.4	KG	1.1
MB-500	Hanger - Glass - Quartz Beige Powder-Coated Steel with Semi-Permanent VHB Tape	Not Pictured	IN	22.00	4.62	0.56	LB	1.0
			CM	55.9	11.7	1.4	KG	0.4
MB-510	Hanger - Wall - Quartz Beige Powder-Coated Steel	17	IN	5.50	2.62	0.56	LB	0.2
			CM	14.0	6.7	1.4	KG	0.1
MB-600	Hanger - Door - Standard - Quartz Beige Powder-Coated Steel	10	IN	5.50	12.13	3.03	LB	1.1
			CM	14.0	30.8	7.6	KG	0.5
MB-601	Hanger - Door - Long - Quartz Beige Powder-Coated Steel	Referenced: 10	IN	5.50	19.00	3.03	LB	1.4
			CM	14.0	48.3	7.6	KG	0.6
MD-100	Dental Organizer - Quartz Beige ABS Plastic & Clear PETG Plastic	71	IN	17.61	23.50	5.08	LB	4.4
			CM	44.7	59.7	12.9	KG	2.0
MP-015	Caddy Dispenser - Clip-On - Clear PETG Plastic	Not Pictured	IN	6.20	7.33	6.65	LB	0.9
			CM	15.7	18.6	16.9	KG	0.4
MP-035	Sign Holder for FM001-0213 - Clear PETG Plastic	53	IN	8.50	11.90	0.38	LB	0.9
			CM	21.6	28.4	1.0	KG	0.4
MP-047	Sign Holder - Clip-On - Clear PETG Plastic	11, 16, 19, 20, 80, 81	IN	8.50	11.16	0.55	LB	0.8
			CM	21.6	28.3	1.3	KG	0.3
MP-070	Sign Holder - Vertical - Clear PETG Plastic	70	IN	8.63	13.36	0.34	LB	1.1
			CM	21.9	35.0	0.9	KG	0.5

*IMPORTED

Part Number	Product Name	Page	Unit	W (L)	H	D	Product Weight	
MP-075	Sign Holder - Horizontal - Clear PETG Plastic	25, 70	IN	11.00	10.90	0.34	LB	1.2
			CM	28.6	28.7	0.9	KG	0.5
MP-085	Caddy Dispenser - Clip-On - Clear PETG Plastic	Not Pictured	IN	4.80	8.10	5.05	LB	0.9
			CM	12.2	20.6	12.8	KG	0.4
MW-001*	Biohazard Bag Holder - 1 Gallon - White Coated-Wire	69	IN	9.50	12.88	6.25	LB	1.7
			CM	24.1	32.7	15.9	KG	0.7
MW-003*	Biohazard Bag Holder - 3 Gallon - White Coated-Wire	69	IN	11.75	15.25	8.00	LB	2.1
			CM	29.8	38.7	20.3	KG	1.0
MW-005*	Biohazard Bag Holder - 5 Gallon - White Coated-Wire	69	IN	13.50	19.50	8.50	LB	2.7
			CM	34.3	49.5	21.6	KG	1.2
NC001-0512	Bedpan/Urinal Dispenser - Quartz Beige Powder-Coated Aluminum	67, 77	IN	12.33	12.00	4.66	LB	1.9
			CM	31.3	30.5	11.8	KG	0.8
NC010-0111	CPR Dispenser - Clear PETG Plastic	69	IN	5.20	2.85	2.50	LB	0.2
			CM	13.2	7.2	6.4	KG	0.1
NC012-0412	Bedpan/Urinal Dispenser - Quartz Beige Powder-Coated Steel	67	IN	12.33	12.00	4.14	LB	3.6
			CM	31.3	30.5	10.5	KG	1.6
PD100-0212	Protection Dispenser - Universal Boxed - Shoe Cover/Cap/Other - Standard - Quartz Beige ABS Plastic	64, 65	IN	12.25	10.13	7.63	LB	1.8
			CM	31.1	25.7	19.4	KG	0.8
PD200-0212	Protection Dispenser - Universal Boxed - Shoe Cover/Cap/Other - Large - Quartz Beige ABS Plastic	64, 65	IN	12.50	10.13	9.88	LB	1.9
			CM	31.8	25.7	25.1	KG	0.8
PD300-0212	Protection Dispenser - Universal Boxed - Shoe Cover/Cap/Other - Wide - Quartz Beige ABS Plastic	64, 65	IN	13.70	5.73	6.95	LB	1.0
			CM	34.8	14.6	17.7	KG	0.5
PS001-0212	Protection System - With Door - Quartz Beige ABS Plastic	9, 13	IN	22.75	20.63	4.86	LB	5.2
			CM	57.7	52.4	12.3	KG	2.3
PS004-0111	Protection System - Glove & Bag - Clear PETG Plastic	Referenced: 47	IN	10.10	20.40	3.95	LB	1.2
			CM	25.7	51.8	10.0	KG	0.5
PS004-0212	Protection System - Glove & Bag - Quartz Beige ABS Plastic	47, 68	IN	10.10	20.40	3.95	LB	1.3
			CM	25.7	51.8	10.0	KG	0.6
PS012-0512	Protection System - Quad Glove - Quartz Beige Powder-Coated Aluminum	Not Pictured	IN	22.75	25.63	4.58	LB	7.3
			CM	57.8	65.1	11.6	KG	3.3
PS014-0212	Protection System - Gloveless - Quartz Beige ABS Plastic	9, 13	IN	23.38	14.98	4.75	LB	4.2
			CM	59.4	38.0	12.1	KG	1.9
PS015-0212	Protection System - Double Gown - Quartz Beige ABS Plastic	9, 13	IN	25.07	30.75	4.75	LB	9.4
			CM	63.3	78.1	12.1	KG	4.3
PS015-0512	Protection System - Double Gown - Quartz Beige Powder-Coated Aluminum	Referenced: 9	IN	25.05	30.75	4.65	LB	11.0
			CM	63.6	78.1	11.8	KG	5.0
PS016-0111	Protection System - Clear PETG Plastic	8	IN	23.38	26.63	4.75	LB	3.1
			CM	59.4	67.6	12.1	KG	1.4
PS016-0212	Protection System - Quartz Beige ABS Plastic	8, 13	IN	23.38	26.63	4.75	LB	7.7
			CM	59.4	67.6	12.1	KG	3.5
PS016-0223	Protection System - Maple Fauxwood ABS Plastic	8	IN	23.38	26.63	4.75	LB	7.8
			CM	59.4	67.6	12.1	KG	3.5
PS016-0233	Protection System - Cherry Fauxwood ABS Plastic	8	IN	23.38	26.63	4.75	LB	7.8
			CM	59.4	67.6	12.1	KG	3.5
PS016-0300	Protection System - Stainless Steel	8	IN	22.75	25.63	4.52	LB	13.2
			CM	57.8	65.1	11.5	KG	7.3
PS016-0512	Protection System - Quartz Beige Powder-Coated Aluminum	8	IN	22.75	25.63	4.58	LB	7.6
			CM	57.8	65.1	11.6	KG	3.4

*IMPORTED