

PermaSleeve® Wire Markers

B-7641 LSZH PermaSleeve Wire Markers:

Use the tables below to browse standard white sleeves or build your own on page 206.

2" Sleeve Width, Single-sided Printable

Compatible Printers: i7100, PR+, BBP72

Recommended Ribbons: R6000, R6600

Catalog #	Color	Sleeves Per Roll	Approx. Wire Gauge	Range of Wire Diameter Inch (mm)		Supplied Diameter Inch (mm)	Recovered Diameter Inch (mm)	Recovered Wall Thickness Inch (mm)	Sleeve Width Inch (mm)
				Min.	Max.				
LSZH-094-2-WT-S	White	500	24 to 20	0.047 (1.2) - 0.080 (2.0)		0.094 (2.4)	0.047 (1.2)	.021 (0.5) ± .004 (0.1)	2,000 (50.8)
LSZH-094-2-WT	White	2,500	24 to 20	0.047 (1.2) - 0.080 (2.0)		0.094 (2.4)	0.047 (1.2)	.021 (0.5) ± .004 (0.1)	2,000 (50.8)
ZH-094-2-WT-J	White	10,000	24 to 20	0.047 (1.2) - 0.080 (2.0)		0.094 (2.4)	0.047 (1.2)	.021 (0.5) ± .004 (0.1)	2,000 (50.8)
LSZH-125-2-WT-S	White	500	20 to 16	0.062 (1.6) - 0.110 (2.8)		0.125 (3.2)	0.063 (1.6)	.025 (0.6) ± .003 (0.07)	2,000 (50.8)
LSZH-125-2-WT	White	2,500	20 to 16	0.062 (1.6) - 0.110 (2.8)		0.125 (3.2)	0.063 (1.6)	.025 (0.6) ± .003 (0.07)	2,000 (50.8)
ZH-125-2-WT-J	White	10,000	20 to 16	0.062 (1.6) - 0.110 (2.8)		0.125 (3.2)	0.063 (1.6)	.025 (0.6) ± .003 (0.07)	2,000 (50.8)
LSZH-187-2-WT-S	White	500	16 to 10	0.094 (2.4) - 0.151 (3.8)		0.187 (4.8)	0.094 (2.4)	.025 (0.6) ± .003 (0.07)	2,000 (50.8)
LSZH-187-2-WT	White	2,500	16 to 10	0.094 (2.4) - 0.151 (3.8)		0.187 (4.8)	0.094 (2.4)	.025 (0.6) ± .003 (0.07)	2,000 (50.8)
ZH-187-2-WT-J	White	10,000	16 to 10	0.094 (2.4) - 0.151 (3.8)		0.187 (4.8)	0.094 (2.4)	.025 (0.6) ± .003 (0.07)	2,000 (50.8)
LSZH-250-2-WT-S	White	250	12 to 8	0.125 (3.2) - 0.215 (5.5)		0.250 (6.4)	0.126 (3.2)	.029 (0.7) ± .003 (0.07)	2,000 (50.8)
LSZH-250-2-WT	White	1,000	12 to 8	0.125 (3.2) - 0.215 (5.5)		0.250 (6.4)	0.126 (3.2)	.029 (0.7) ± .003 (0.07)	2,000 (50.8)
ZH-250-2-WT-J	White	7,500	12 to 8	0.125 (3.2) - 0.215 (5.5)		0.250 (6.4)	0.126 (3.2)	.029 (0.7) ± .003 (0.07)	2,000 (50.8)
LSZH-375-2-WT-S	White	250	8 to 4	0.188 (4.8) - 0.320 (8.1)		0.375 (9.5)	0.189 (4.8)	.028 (0.7) ± .002 (0.05)	2,000 (50.8)
LSZH-375-2-WT	White	1,000	8 to 4	0.188 (4.8) - 0.320 (8.1)		0.375 (9.5)	0.189 (4.8)	.028 (0.7) ± .002 (0.05)	2,000 (50.8)
ZH-375-2-WT-J	White	5,000	8 to 4	0.188 (4.8) - 0.320 (8.1)		0.375 (9.5)	0.189 (4.8)	.028 (0.7) ± .002 (0.05)	2,000 (50.8)
LSZH-500-2-WT-S	White	250	6 to 1	0.250 (6.4) - 0.450 (11.4)		0.500 (12.7)	0.252 (6.4)	.028 (0.7) ± .002 (0.05)	2,000 (50.8)
LSZH-500-2-WT	White	500	6 to 1	0.250 (6.4) - 0.450 (11.4)		0.500 (12.7)	0.252 (6.4)	.028 (0.7) ± .002 (0.05)	2,000 (50.8)
ZH-500-2-WT-J	White	2,500	6 to 1	0.250 (6.4) - 0.450 (11.4)		0.500 (12.7)	0.252 (6.4)	.028 (0.7) ± .002 (0.05)	2,000 (50.8)
LSZH-750-2-WT-S	White	100	2 to 4/0	0.375 (9.5) - 0.700 (17.8)		0.750 (19.0)	0.375 (9.5)	.031 (0.8) ± .003 (0.07)	2,000 (50.8)
LSZH-750-2-WT	White	250	2 to 4/0	0.375 (9.5) - 0.700 (17.8)		0.750 (19.0)	0.375 (9.5)	.031 (0.8) ± .003 (0.07)	2,000 (50.8)
ZH-750-2-WT-J	White	2,500	2 to 4/0	0.375 (9.5) - 0.700 (17.8)		0.750 (19.0)	0.375 (9.5)	.031 (0.8) ± .003 (0.07)	2,000 (50.8)
LSZH-1000-2-WT-S	White	100	2/0 to 0.950" dia.	0.450 (11.4) - 0.950 (24.1)		1.000 (25.4)	0.500 (12.7)	.036 (0.9) ± .003 (0.07)	2,000 (50.8)
LSZH-1000-2-WT	White	250	2/0 to 0.950" dia.	0.450 (11.4) - 0.950 (24.1)		1.000 (25.4)	0.500 (12.7)	.036 (0.9) ± .003 (0.07)	2,000 (50.8)
ZH-1000-2-WT-J	White	2,500	2/0 to 0.950" dia.	0.450 (11.4) - 0.950 (24.1)		1.000 (25.4)	0.500 (12.7)	.036 (0.9) ± .003 (0.07)	2,000 (50.8)
LSZH-1500-2-WT	White	250	N/A	0.750 (19.0) - 1.400 (35.6)		1.500 (38.1)	0.752 (19.1)	.038 (1.0) ± .003 (0.07)	2,000 (50.8)
ZH-1500-2-WT-J	White	1,000	N/A	0.750 (19.0) - 1.400 (35.6)		1.500 (38.1)	0.752 (19.1)	.038 (1.0) ± .003 (0.07)	2,000 (50.8)
LSZH-2000-2-WT-S	White	50	N/A	1.000 (25.4) - 1.900 (48.3)		2.000 (50.8)	1.000 (25.4)	.038 (1.0) ± .003 (0.07)	2,000 (50.8)
LSZH-2000-2-WT	White	100	N/A	1.000 (25.4) - 1.900 (48.3)		2.000 (50.8)	1.000 (25.4)	.038 (1.0) ± .003 (0.07)	2,000 (50.8)
ZH-2000-2-WT-J	White	1,000	N/A	1.000 (25.4) - 1.900 (48.3)		2.000 (50.8)	1.000 (25.4)	.038 (1.0) ± .003 (0.07)	2,000 (50.8)

3" Sleeve Width, Single-sided Printable

Compatible Printers: i7100, PR+, BBP72

Recommended Ribbons: R6000, R6600

Catalog #	Color	Sleeves Per Roll	Approx. Wire Gauge	Range of Wire Diameter Inch (mm)		Supplied Diameter Inch (mm)	Recovered Diameter Inch (mm)	Recovered Wall Thickness Inch (mm)	Sleeve Width Inch (mm)
				Min.	Max.				
ZH-1000-3-WT	White	250	2/0 to 0.950" dia.	0.450 (11.4) - 0.950 (24.1)		1.000 (25.4)	0.500 (12.7)	.036 (0.9) ± .003 (0.07)	3,000 (76.2)
ZH-1500-3-WT	White	250	N/A	0.750 (19.0) - 1.400 (35.6)		1.500 (38.1)	0.752 (19.1)	.038 (1.0) ± .003 (0.07)	3,000 (76.2)
LSZH-2000-3-WT	White	100	N/A	1.000 (25.4) - 1.900 (48.3)		2.000 (50.8)	1.000 (25.4)	.038 (1.0) ± .003 (0.07)	3,000 (76.2)

3" Core Materials

PermaSleeves