



Straight Blade Devices, Receptacles, Flush Mount Single, Commercial/Industrial Grade, Reinforced Thermoplastic Polyester, 30A 250V

By Bryant
Catalog # 9630IG

Straight Blade Devices, Receptacles, Flush Mount Single, Commercial/Industrial Grade, Reinforced Thermoplastic Polyester, 30A 250V, 2-Pole 3-Wire Grounding, 6-30R, Orange, Single Pack, Isolated Ground

Features

- Flush Mount Single
- Commercial/Industrial Grade
- Reinforced Thermoplastic Polyester
- 30A 250V
- 2-Pole 3-Wire Grounding

Application

Industrial Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	6-30R
Industry Standard(s)	WR Rating

Conductor

Number Of Wires	3-Wire
Wire Size	#10 AWG to #6 AWG
Number Of Poles	2-Pole

Current

Amperage Rating	30 A
Voltage Rating Description	250 V
Current Rating	30 A
Voltage Rating	250 V



Wattage	7500
Connectivity	Pressure Terminal Screws
Phase	Single Phase
Current / Amperage Rating	30 A

Dimensions

Display Size	Standard Sized Product
Weight	0.35 lb.

General

Color	Orange
Style	Extra Heavy Duty
Series	Straight Blade
OEM Brand Name	Hubbell Bryant
UPC	781786731080
Type	Single Receptacle
Material - Mounting Hardware	Screw Mounting
Item Type	Single
Material	Composite

Logistics

Carton Quantity	25
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)