



Straight Blade Devices, Receptacle Cordsets, Receptacle with Pilot Light, Commercial/Industrial, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, 6' Cord

By Bryant
Catalog # [T1254GF6](#)

Straight Blade Devices, Receptacle Cordsets, Receptacle with Pilot Light, Commercial/Industrial, 15A 125V, 2-Pole 3- Wire Grounding, 5-15R, 6' Cord, Yellow, Single Pack



Features

- Receptacle with Pilot Light
- Commercial/Industrial
- 15A 125V
- 2-Pole 3- Wire Grounding
- 5-15R

Application

Commercial/Industrial

Specifications

Environmental Conditions Indoor Dry Unless Protected By Additional Means

Conductor

Wire Size #14 AWG to #12 AWG

Current

Amperage Rating 15 A
Voltage Rating Description 120 V
Current Rating 15 A
Voltage Rating 120 V
Wattage 1875
Phase Single Phase

Current / Amperage Rating 15 A

Dimensions

Display Size Standard Sized Product
Weight 1.7 lb.

General

Color Yellow
Style Cord Sets
Series Commercial
OEM Brand Name Hubbell Bryant
UPC 781786181007
Type Four Outlet Receptacle
Material - Mounting Hardware Screw Mounting
Item Type Quad-Plex Cord Set
Material Composite

Logistics

Carton Quantity 5

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)