

# WIRETWIST®

## WIRE CONNECTORS

### FIXED-SPRING

The price is right for this economical connector that brings a lot of value in comfort and performance.

Developed for projects on tight budgets.

**FAST FACT**

Tough, UL 94V-2 flame-retardant shell rated at 105°C (221°F)



Positive grip shell design for fast, easy installation

Multiple sizes accommodate a broad range of electrical applications

#### Ordering Information

Model	Quantity	Cat. No.
 WT1 Gray Min. 3 #22 - Max. 2 #16	Box of 100	<b>WT1-1</b>
	Bag of 500	<b>WT1-B</b>
 WT2 Blue Min. 3 #20 - Max. 3 #16	Box of 100	<b>WT2-1</b>
	Bag of 500	<b>WT2-B</b>
	Barrel of 50,000	<b>WT2-SK</b>
 WT3 Orange Min. 2 #18 - Max. 2 #14	Box of 100	<b>WT3-1</b>
	Bag of 500	<b>WT3-B</b>
	Barrel of 50,000	<b>WT3-SK</b>
 WT4 Yellow Min. 3 #20 - Max. 2 #12	Box of 100	<b>WT4-1</b>
	Bag of 500	<b>WT4-B</b>
 WT6 Red Min. 2 #14 - Max. 4 #12	Box of 100	<b>WT6-1</b>
	Bag of 250	<b>WT6-B</b>

#### WireTwist® Wire Connector

600V. Max.\*  
105°C (221°F)

WT1 Gray (300V)	Min. 3 #22								Max. 2 #16
WT2 Blue (300V)		Min. 3 #20							Max. 3 #16
WT3 Orange (600V*)			Min. 2 #18						Max. 2 #14
WT4 Yellow (600V*)		Min. 3 #20							Max. 2 #12
WT6 Red (600V*)								Min. 2 #14	Max. 4 #12

#### Wire Combinations:

3 #22    3 #20    2 #18    2 #16    2 #14    2 #12    4 #12



\*1,000 Volts signs and fixtures.

Made in Canada.

