

102009T, Shear Bolt Stirrup Connector

By Burndy
Catalog # [102009T](#)

Conductor Range: 2/0 - 4/0 AAC (.414"-.522") With 1/0 Tin Plated Bail (.313") Tin Plated

Features

- Easy to remove and re-use without damaging the conductor
- Heavy duty tin plated bail has a large loop to allow for multiple connection positions while also eliminating galvanic reaction
- Easy to install with standard socket or impact wrench, requires no special tools
- Easy adaptable to standard hot stick tools
- High-conductivity grit corrosion inhibitor is factory applied for ease of installation and longevity while the connector is in service
- Remains permanently locked through fault current or power surges
- May be used in non-corrosive environments to connect copper conductors



- Excellent option for emergency restoration

General

Catalog Number	102009T
Type	Stirrups
UPC	621945675025

Conductor Related

Conductor Range	Main Conductor: 2/0-4/0 AAC, 1/0 Bail
-----------------	--

Product Assets

[Installation Manuals - Hot-Stick Stirrup Installation Instructions](#)
[Specifications - 102009T](#)