

102011T, Tin Plated Shear Bolt Stirrup Connector

By Burndy
Catalog # [102011T](#)



Conductor Range: #6 - #2 AAC (.162"-.292") With 1/0 Tin Plated
Bail (.313") Tin Plated

Features

- Easy to remove and re-use without damaging the conductor
- Heavy duty tin plated bail has a large loop to allow for multiple connection positions while also eliminating galvanic reaction
- Easy to install with standard socket or impact wrench, requires no special tools
- Easy adaptable to standard hot stick tools
- High-conductivity grit corrosion inhibitor is factory applied for ease of installation and longevity while the connector is in service
- Remains permanently locked through fault current or power surges
- May be used in non-corrosive environments to connect copper conductors

- Excellent option for emergency restoration

General

Catalog Number	102011T
Type	Stirrups
UPC	621945675315

Conductor Related

Conductor Range	Main Conductor: #6-#2 AAC, 1/0 Bail
-----------------	--

Product Assets

[Installation Manuals - Hot-Stick Stirrup Installation Instructions](#)
[Specifications - 102011T](#)