



159404, XL Shear Bolt WEJTAP™ Connector

By Burndy
Catalog # [159404](#)



Main Conductor: 1590 ACSR (1.502" - 1.545") Tap Conductor: 4/0 ACSR (.563")

Features

- Industry-proven spring wedge technology easily installed with common socket or impact wrench - No Special Tools Required!
- "Spring Like" high strength C-Body ensures permanent connection with consistent pressure on the conductors
- Meets or exceeds current carrying capacity of conductors being connected
- Corrosion resistant highly conductive aluminum alloys with a pure aluminum insert between conductors increases conductivity and lowers electrical resistance
- Corrosion inhibitor factory applied for ease of installation
- Remains permanently locked through fault current or power surges
- Easy to remove without damage to conductor
- May be used in non-corrosive environments to connect copper conductors

- Excellent option for emergency storm restoration

General

Catalog Number	159404
UPC	621945682993

Conductor Related

Conductor Range	Main Conductor: 1590 ACSR, Tap: 4/0 ACSR
-----------------	---

Product Assets

[Excel Files - Burndy-CPI WEJTAP Connector Selector](#)
[Installation Manuals - Tap Connector Installation Instructions](#)
[Specifications - 159404](#)
[Video - WEJTAP™ Installation with Gloves](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-159404-SPEC-EN | REV 7/2025