



**1PL3502, UV Rated Black, 1-Sided, 2-Port,
#10 AWG-350 kcmil**

By Burndy
Catalog # [1PL3502](#)

UV Rated Covering, Oxide inhibitor pre-installed, Same-Side, 2-Port Tap,
#10 AWG-350 kcmil

Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

Application

For Indoor Use Only, Copper Or Stranded Aluminum

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct	No
Burial	
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil
Conductor - AL Str Size Range	10 AWG - 350 kcmil
Conductor - Copper Str Size	• 10 AWG • 9 AWG

- 8 AWG
 - 7 AWG
 - 6 AWG
 - 5 AWG
 - 4 AWG
 - 3 AWG
 - 2 AWG
 - 1 AWG
 - 1/0
 - 2/0 AWG
 - 3/0 AWG
 - 4/0 AWG
 - 250 kcmil
 - 300 kcmil
 - 350 kcmil
- Conductor Size 10 AWG-350 KCMIL
- Conductor Type
- AL C Str-Size
 - CU C Str-Size
- Conductor - Copper Str Size Range 10 AWG - 350 kcmil

Configuration

Physical Attribute - Number of Screws	2
Number Of Ports	2
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	63.5 mm
Dimension - Height inch	2.50 in
Dimension - Height fraction	2-1/2 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	63
Width	2.32 in
Dimension - Width fraction	2-8/25 in
Length	2.47 in
Dimension - Width mm	59 mm
Dimension - Width inch	2.32 in
Height	2.5 in
Dimension - Length Overall inch	2.47
Dimensions	2.47 in x 2.32 in x 2.5 in

Force Related

Installation Torque Recommended 275 in-lb
in-lb

General

Product Family MECHANICAL
Insulation Type Platisol
Trade Name UNITAP™
Material - Hardware Aluminum
Insulation Y
Physical Attribute - Screw Type Allen
Plated No
Sub Brand UNITAP
Product Type Run/Tap
UPC 781810370117
Type BIBS, Multi-Port
Hex Key 5/16



A Hubbell brand

Material Aluminum
Plating Type Unplated
UPC 12 Digit 781810370117
UPC 14 Digit GTIN 00781810370117

Logistics

Minimum Pack Quantity 1
Pallet Quantity 1920
Carton Quantity 20

Operational

Temperature Rating 194° F

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)