



1PL44, UV Rated Black, 1-Sided, 4-Port, #14-4 AWG

By Burndy
Catalog # [1PL44](#)

UV Rated Covering, Oxide inhibitor pre-installed, Same-Side, 4-Port Tap, #14-4 AWG

Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

Application


For Indoor Use Only, Copper Or Stranded Aluminum

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 14 AWG • 12 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG
Conductor - AL Str Size Range	14 AWG - 4 AWG
Conductor - Copper Str Size	• 14 AWG • 12 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG
Conductor Size	14-4 AWG
Conductor Type	• AL C Str-Size



Conductor - Copper Str Size Range	• CU C Str-Size 14 AWG - 4 AWG
-----------------------------------	--

Configuration

Physical Attribute - Number of Screws	4
Number Of Ports	4
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	31.8 mm
Dimension - Height inch	1.25 in
Dimension - Height fraction	1.25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	50 mm
Width	1.25 in
Dimension - Width fraction	1-1/4 in
Dimension - Screw Size inch Length	1/4
Dimension - Width mm	32 mm
Dimension - Width inch	1.25 in
Height	1.25 in
Dimension - Length Overall inch	1.95 in
Dimensions	1.95 in x 1.25 in x 1.25 in

Force Related

Installation Torque Recommended in-lb	45 in-lb
---------------------------------------	----------

General

Insulation Type	Plastisol
Trade Name	UNITAP™
Material - Hardware	Aluminum
Insulation	Y
Physical Attribute - Screw Type Plated	Allen N

Sub Brand	UNITAP	Pallet Quantity	11200
UPC	781810286982	Carton Quantity	200
Type	BIBS, Multi-Port	Operational	
Hex Key	1/8		
Material	Aluminum	Temperature Rating	194° F
Plating Type	Unplated	Product Assets	
UPC 12 Digit	781810286982	Catalog [English]	
UPC 14 Digit GTIN	00781810286982	Catalog [English]	
Logistics			

