



1PL7503, UV Rated Black, 1-Sided, 3-Port, #2 AWG-750 kcmil

By Burndy
Catalog # [1PL7503](#)

UV Rated Covering, Oxide inhibitor pre-installed, Same-Side, 3-Port Tap, #2 AWG-750 kcmil

Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil • 550 kcmil • 556 kcmil • 600 kcmil • 636 kcmil • 650 kcmil • 700 kcmil • 715 kcmil • 750 kcmil
Conductor - AL Str Size Range	2 AWG - 750 kcmil



Conductor - Copper Str Size	• 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil • 700 kcmil • 750 kcmil
Conductor Size	2 AWG-750 KCMIL
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	2 AWG - 750 kcmil

Configuration

Physical Attribute - Number of Screws	3
Number Of Ports	3
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	76.2 mm
Dimension - Height inch	3.00 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	102 mm
Width	2.7 in
Dimension - Screw Size inch	13/16
Length	4 in
Dimension - Width mm	69 mm
Dimension - Width inch	2.70 in
Height	3 in

Dimension - Length Overall inch	4.00 in	Material	Aluminum
Dimensions	4 in x 2.7 in x 3 in	Plating Type	Unplated
		UPC 12 Digit	781810287071
		UPC 14 Digit GTIN	00781810287071
Force Related		Logistics	
Installation Torque Recommended in-lb	375 in-lb	Minimum Pack Quantity	1
		Pallet Quantity	1080
		Carton Quantity	40
General		Operational	
Insulation Type	Plastisol	Temperature Rating	194° F
Trade Name	UNITAP™		
Material - Hardware	Aluminum		
Insulation	Y		
Physical Attribute - Screw Type	Allen		
Plated	N		
UPC	781810287071	Product Assets	
Hex Key	3/8	Catalog [English]	
		Catalog [English]	



A Hubbell brand