



**1PLD2503, UV Rated Black, 2-Side, 3-Port,
#10 AWG-250 kcmil**

By Burndy
Catalog # [1PLD2503](#)

UV Rated Covering, Oxide inhibitor pre-installed 2-Sided, 3-Port Tap, #10
AWG-250 kcmil

Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

Application

For Indoor Use Only, Copper Or Stranded Aluminum

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	EX
Status	
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil
Conductor - AL Str Size Range	10 AWG - 250 kcmil
Conductor - Copper Str Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG



- 5 AWG
 - 4 AWG
 - 3 AWG
 - 2 AWG
 - 1 AWG
 - 1/0
 - 2/0 AWG
 - 3/0 AWG
 - 4/0 AWG
 - 250 kcmil
- Conductor Size 10 AWG-250 KCMIL
- Conductor Type
 - AL C Str-Size
 - CU C Str-Size
- Conductor - Copper Str Size Range 10 AWG - 250 kcmil

Configuration

Physical Attribute - Number of Screws	3
Number Of Ports	3
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	54.1 mm
Dimension - Height inch	2.13 in
Dimension - Height fraction	2.125 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	75 mm
Width	2.64 in
Dimension - Width fraction	2-16/25 in
Dimension - Screw Size inch	5/8
Length	2.97 in
Dimension - Width mm	67 mm
Dimension - Width inch	2.64 in
Height	2.13 in
Dimension - Length Overall inch	2.97 in
Dimensions	2.97 in x 2.64 in x 2.13 in

Force Related

Installation Torque Recommended 275 in-lb
in-lb

General

Product Family	MECHANICAL
Insulation Type	Plastisol
Trade Name	UNITAP™
Material - Hardware	Aluminum
Insulation	Y
Physical Attribute - Screw Type	Allen
Plated	No
Sub Brand	UNITAP
Product Type	Run/Tap
UPC	781810287170
Type	BIBD, Multi-Port
Hex Key	5/16

Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810287170
UPC 14 Digit GTIN	00781810287170

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1536
Carton Quantity	24

Operational

Temperature Rating	194° F
--------------------	--------

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)



A Hubbell brand