




1PLD35012, UV Rated Black, 2-Side, 12-Port,
10 AWG-350 kcmil

By Burndy
Catalog # [1PLD35012](#)

UV Rated Covering, Oxide inhibitor pre-installed 2-Sided, 12-Port
Tap, #10 AWG-350 kcmil



Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil
Conductor - AL Str Size Range	10 AWG - 350 kcmil
Conductor - Copper Str Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG

- 3 AWG
 - 2 AWG
 - 1 AWG
 - 1/0
 - 2/0 AWG
 - 3/0 AWG
 - 4/0 AWG
 - 250 kcmil
 - 300 kcmil
 - 350 kcmil
- 10 AWG-350 KCMIL
- AL C Str-Size
 - CU C Str-Size

Conductor Size	10 AWG-350 KCMIL
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	10 AWG - 350 kcmil

Configuration

Physical Attribute - Number of Screws	12
Number Of Ports	12
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	63.5 mm
Dimension - Height inch	2.50 in
Dimension - Height fraction	2.5 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	288 mm
Width	3 in
Dimension - Screw Size inch	11/16
Length	11.32 in
Dimension - Width mm	76 mm
Dimension - Width inch	3.00 in
Height	2.5 in
Dimension - Length Overall inch	11.32 in
Dimensions	11.32 in x 3 in x 2.5 in

Force Related

Installation Torque	275 in-lb	UPC 12 Digit	781810287323
Recommended in-lb		UPC 14 Digit GTIN	00781810287323
General		Logistics	
Insulation Type	Plastisol	Minimum Pack Quantity	1
Trade Name	UNITAP™	Pallet Quantity	648
Material - Hardware	Aluminum	Carton Quantity	24
Insulation	Y	Operational	
Physical Attribute - Screw Type	Allen	Temperature Rating	194° F
Plated	N	Product Assets	
UPC	781810287323	Catalog [English]	
Hex Key	5/16	Catalog [English]	
Material	Aluminum		
Plating Type	Unplated		



A Hubbell brand