



**1PLD3503, UV Rated Black, 2-Side, 3-Port,
#10 AWG-350 kcmil**

By Burndy
Catalog # [1PLD3503](#)

UV Rated Covering, Oxide inhibitor pre-installed 2-Sided, 3-Port Tap, #10
AWG-350 kcmil

Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

Application

For Indoor Use Only, Copper Or Stranded Aluminum

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct	No
Burial	
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil
Conductor - AL Str Size Range	10 AWG - 350 kcmil
Conductor - Copper Str Size	• 10 AWG • 9 AWG • 8 AWG



- 7 AWG
 - 6 AWG
 - 5 AWG
 - 4 AWG
 - 3 AWG
 - 2 AWG
 - 1 AWG
 - 1/0
 - 2/0 AWG
 - 3/0 AWG
 - 4/0 AWG
 - 250 kcmil
 - 300 kcmil
 - 350 kcmil
- Conductor Size 10 AWG-350 KCMIL
- Conductor Type
- AL C Str-Size
 - CU C Str-Size
- Conductor - Copper Str Size Range 10 AWG - 350 kcmil

Configuration

Physical Attribute - Number of Screws	3
Number Of Ports	3
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	63.5 mm
Dimension - Height inch	2.50 in
Dimension - Height fraction	2.5 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	80 mm
Width	3 in
Dimension - Screw Size inch	11/16
Length	3.13 in
Dimension - Width mm	76 mm
Dimension - Width inch	3.00 in
Height	2.5 in
Dimension - Length Overall inch	3.13 in
Dimensions	3.13 in x 3 in x 2.5 in

Force Related

Installation Torque Recommended 275 in-lb
in-lb

General

Product Family MECHANICAL
Insulation Type Plastisol
Trade Name UNITAP™
Material - Hardware Aluminum
Insulation Y
Physical Attribute - Screw Type Allen
Plated No
Sub Brand UNITAP
Product Type Run/Tap
UPC 781810287262
Type BIBD, Multi-Port
Hex Key 5/16



A Hubbell brand

Material Aluminum
Plating Type Unplated
UPC 12 Digit 781810287262
UPC 14 Digit GTIN 00781810287262

Logistics

Minimum Pack Quantity 1
Pallet Quantity 1728
Carton Quantity 24

Operational

Temperature Rating 194° F

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)