



1PLD6002, UV Rated Black, 2-Sided, 2-Ports, #4 AWG-600 kcmil

By Burndy
Catalog # 1PLD6002

UV Rated Covering, Oxide inhibitor pre-installed 2-Sided, 2-Port Tap, #4 AWG-600 kcmil

Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

Application

For Indoor Use Only, Copper Or Stranded Aluminum

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil • 550 kcmil • 556 kcmil • 600 kcmil
-------------------------	---



Conductor - AL Str Size Range	4 AWG - 600 kcmil
Conductor - Copper Str Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil
Conductor Size	4 AWG-600 KCMIL
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	4 AWG - 600 kcmil

Configuration

Physical Attribute - Number of Screws	2
Number Of Ports	2
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	69.9 mm
Dimension - Height inch	2.75 in
Dimension - Height fraction	2.75 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	69 mm
Width	3 in
Dimension - Screw Size inch	13/16
Length	2.72 in
Dimension - Width mm	76 mm

Dimension - Width inch	3.00 in
Height	2.75 in
Dimension - Length Overall inch	2.72 in
Dimensions	2.72 in x 3 in x 2.75 in

Force Related

Installation Torque	375 LBS/in
Recommended in-lb	

General

Insulation Type	Plastisol
Trade Name	UNITAP™
Material - Hardware	Aluminum
Insulation	Y
Physical Attribute - Screw Type	Allen
Plated	N
Sub Brand	UNITAP

UPC	781810287330
Type	BIBD, Multi-Port
Hex Key	3/8
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810287330
UPC 14 Digit GTIN	00781810287330

Logistics

Pallet Quantity	1
Carton Quantity	45

Operational

Temperature Rating	194
--------------------	-----

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)



A Hubbell brand