



1PLD7502HD, UV Rated Black, 2-sided, 2-port, #2 AWG-750 kcmil

By Burndy
Catalog # [1PLD7502HD](#)

UV Rated, Black UNITAP™; PL = Single Sided Entry; PLO = Offset Entry

Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	Yes

Conductor

Conductor Size	2 AWG-750 KCMIL
----------------	-----------------

Configuration

Connector Type	Multi Tap
Number Of Ports	2

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - L Length Overall	66.802 mm
------------------------------	-----------



Length	2.63 in
Dimension - Length Overall	2.63 inch
Width	4.83 in
Height	3 in
Dimensions	2.63 in x 4.83 in x 3 in

Force Related

Installation Torque	500 in-lb
Recommended in-lb	

General

Trade Name	UNITAP™
Material	Aluminum
Hex Key	3/8 in
UPC	621945480728

Logistics

Minimum Pack Quantity	1
Carton Quantity	24
Pallet Quantity	648

Operational

Temperature Rating	-40°C to 135°C
--------------------	----------------

Product Assets

[Catalog \[English\]](#)