




1PLD7508, UV Rated Black, 2-Sided, 8-Port, #2 AWG-750 kcmil

By Burndy
Catalog # [1PLD7508](#)

UV Rated Covering, Oxide inhibitor pre-installed 2-Sided, 8-Port Tap, #2 AWG-750 kcmil



Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil • 550 kcmil • 556 kcmil • 600 kcmil • 636 kcmil • 650 kcmil • 700 kcmil • 715 kcmil • 750 kcmil
Conductor - AL Str Size Range	2 AWG - 750 kcmil

Conductor - Copper Str Size	• 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil • 700 kcmil • 750 kcmil
Conductor Size	2 AWG-750 KCMIL
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	2 AWG - 750 kcmil

Configuration

Physical Attribute - Number of Screws	8
Number Of Ports	8
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	76.2 mm
Dimension - Height inch	3.00 in
Dimension - Height fraction	3 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	283 mm
Width	3.38 in
Dimension - Screw Size inch	13/16
Length	11.13 in
Dimension - Width mm	86 mm
Dimension - Width inch	3.38 in

Height	3 in
Dimension - Length Overall	11.13 in
inch	
Dimensions	11.13 in x 3.38 in x 3 in

Force Related

Installation Torque	500 in-lb
Recommended in-lb	

General

Insulation Type	Plastisol
Material - Hardware	Aluminum
Insulation	Y
Physical Attribute - Screw Type	Allen
Plated	N
UPC	781810287453

Hex Key	3/8
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810287453
UPC 14 Digit GTIN	00781810287453

Logistics

Minimum Pack Quantity	1
Pallet Quantity	405
Carton Quantity	15

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand