1PLMD6008, UV Black, Mount, 2-Side, 8-Port, 4 AWG-600



By Burndy
Catalog # 1PLMD6008

UV Rated Covering, Oxide inhibitor pre-installed, Mountable, 2-Sided, 8-Port Tap, #4 AWG-600 kcmil

Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes
Certification - UL Listed Direct Burial	No

Conductor

Conductor Size	4 AWG-600 KCMIL
Conductor - Copper Str Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil
Conductor - Copper Str Size Range	4 AWG - 600 kcmil
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - AL Str Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil • 550 kcmil • 556 kcmil • 600 kcmil
Conductor - AL Str Size Range	4 AWG - 600 kcmil

Configuration

Physical Attribute - Number of Screws	8
Connector Type	Multi Tap
Number Of Ports	8

Current

Voltage - Maximum	600 V

Dimensions

Dimension - Width inch	3.00 in
Package Length	0.000 in
Dimension - Width mm	76 mm
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Height fraction	2.75 in
Dimension - Height inch	2.75 in
Package Height	0.000 in
Dimension - Height mm	69.9 mm
Length	12.91 in
Width	3 in
Height	2.75 in
Dimensions	12.91 in x 3 in x 2.75 in

General

Material - Hardware	Aluminum

Physical Attribute - Screw Type	Allen
Insulation Type	Plastisol
Plated	N
Insulation	Y
UPC 12 Digit	781810307830
UPC 14 Digit GTIN	00781810307830
Material	Aluminum
Hex Key	3/8
Plating Type	Unplated
UPC	781810307830

Logistics

Minimum Pack Quantity	1

Operational

Temperature Rating	194

Product Assets

Catalog [English]
Catalog [English]

A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved