



210105T, Shear Bolt WEJTAP™ Connector, Small Series

By Burndy

Catalog # [210105T](#)



Main Conductor: #1 ACSR- 2/0 AAC (.354"- .414") Tap

Conductor: #4 AAC - #1 AAC (.232"- .328") Tin Plated

Features

- Industry-proven spring wedge technology easily installed with common socket or impact wrench
- Installed overhead
- Meets or exceeds current carrying capacity of conductors being connected
- "Spring like" high strength C-Body ensures permanent connection with consistent pressure on the conductors
- Corrosion resistant highly conductive copper and bronze alloys with a pure copper insert between conductors increases conductivity and lower electrical resistance
- Corrosion inhibitor factory applied for ease of installation
- Remains permanently locked through fault current or power surges
- Easy to remove without damage to conductor
- May be used in non-corrosive environments to connect copper conductors

- Excellent option for emergency restoration where outside crews might not have Shoot-On or compression tooling

General

Catalog Number	210105T
UPC	621945675742

Conductor Related

Conductor Range	Main Conductor: #1 ACSR-2/0 AAC, Tap: #4-1 AAC
-----------------	--

Product Assets

[Excel Files - Burndy-CPI WEJTAP Connector Selector](#)
[Installation Manuals - Tap Connector Installation Instructions](#)
[Specifications - 210105T](#)
[Video - WEJTAP™ Installation with Gloves](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-210105T-SPEC-EN | REV 7/2025