

210106T, Shear Bolt WEJTAP™ Connector, Small Series

By Burndy

Catalog # [210106T](#)



Main Conductor: #1 ACSR - 2/0 AAC (.354"-.414") Tap

Conductor: #1 ACSR - 2/0 AAC (.354"-.414") Tin Plated

Features

- Industry-proven spring wedge technology easily installed with common socket or impact wrench
- Installed overhead
- Meets or exceeds current carrying capacity of conductors being connected
- "Spring like" high strength C-Body ensures permanent connection with consistent pressure on the conductors
- Corrosion resistant highly conductive copper and bronze alloys with a pure copper insert between conductors increases conductivity and lower electrical resistance
- Corrosion inhibitor factory applied for ease of installation
- Remains permanently locked through fault current or power surges
- Easy to remove without damage to conductor
- May be used in non-corrosive environments to connect copper conductors

- Excellent option for emergency restoration where outside crews might not have Shoot-On or compression tooling

General

Catalog Number	210106T
UPC	621945675896

Conductor Related

Conductor Range	Main Conductor: #1 ACSR-2/0 AAC, Tap: #1 ACSR-2/0 AAC
-----------------	---

Product Assets

[Excel Files - Burndy-CPI WEJTAP Connector Selector](#)

[Installation Manuals - Tap Connector Installation Instructions](#)

[Specifications - 210106T](#)

[Video - WEJTAP™ Installation with Gloves](#)