



25CHENET, 1/4" Silicon Bronze Hex Nut, Tin Plated

By Burndy
Catalog # 25CHENET

Electro Tin Plated Silicon Bronze 1/4-20 Nut



Features

- Tin Plated DURIMUM™ silicon bronze hardware combines high strength and corrosion resistance
- Silicon bronze per ASTM B99

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Nut
----------------	-----

Dimensions

Package Height	0.000 in
Dimension - Bolt Size fraction	1/4
Length	0.438 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - Outside Diameter	0.44 in
Height	0.226 in
Width	0.505 in
Dimension - Thread Size	1/4 - 20
Dimension - Threads per inch	20
Dimension - Bolt Size inch	0.25 in
Dimensions	0.438 in x 0.505 in x 0.226 in

Force Related

Installation Torque	80 LBS/in
Recommended in-lb	

General

Trade Name	DURIMUM™
UPC	781810120606
Material	Silicon Bronze
UPC 12 Digit	781810120606
UPC 14 Digit GTIN	00781810120606

Logistics

Minimum Pack Quantity	50
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)