



25X125HSSB, 1/4" x 1-1/4" Hex Bolt,
Stainless Steel

By Burndy
Catalog # [25X125HSSB](#)

Stainless Steel Bolt, 1.25 in L, Hexagonal bolts,Thread size:1/4-20

Features

- Stainless Steel hardware is manufactured from 18-8 non-magnetic material
- Nut surfaces and bolt heads have American National Coarse Series, Class #2 fit

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Dimensions

Width	0.25 in
-------	---------



Dimension - Bolt Size fraction	1/4
Length	1.25 in
Dimension - Thread Size	1/4 - 20
Dimension - Threads per inch	20
Dimension - B Length fraction	1-1/4 in
Dimension - Bolt Size inch	0.250 in
Dimension - Length Overall	1.25 in
inch	
Dimension - B Length inch	1.25 in

General

UPC	781810532362
Material	STAINLESS STEEL

Product Assets

[Catalog \[English\]](#)