



25X300HEBET, 1/4" x 3" Hex Bolt, Silicon Bronze, Tin Plated

By Burndy
Catalog # 25X300HEBET

Electro Tin Plated Silicon Bronze Hexagonal Head Bolt, 3.00 IN L, 1/4 IN-20 Thread Size

Features

- DURIMUM™ silicon bronze hardware combines high strength and corrosion resistance
- Silicon bronze per ASTM B99

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Bolt - Hex
----------------	------------

Dimensions

Package Height	0.000 in
Dimension - Bolt Size fraction	1/4
Length	3 in
Dimension - B Length fraction	3 in
Package Weight	0.000 lb.
Package Length	0.000 in



Package Width	0.000 in
Dimension - B Length inch	3 in
Width	0.25 in
Dimension - Thread Size	1/4 - 20
Dimension - Threads per inch	20
Dimension - Bolt Size inch	0.25 in

Force Related

Installation Torque	80 LBS/in
Recommended in-lb	

General

UPC	781810249222
Material	Silicon Bronze
UPC 12 Digit	781810249222
UPC 14 Digit GTIN	00781810249222

Logistics

Minimum Pack Quantity	500
Pallet Quantity	58000
Carton Quantity	500

Product Assets

[Catalog \[English\]](#)