



25X62HEBBOX, 1/4" x 5/8" Hex Bolt, Silicon Bronze

By Burndy
Catalog # [25X62HEBBOX](#)

Silicon Bronze Hexagonal Head Bolt, 0.62 IN L, 1/4 IN-20 Thread Size

Features

- DURIMUM™ silicon bronze hardware combines high strength and corrosion resistance
- Silicon bronze per ASTM B99

Application

Grounding;Distribution;Substation;Transmission

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Bolt - Hex
----------------	------------

Dimensions

Package Height	0.000 in
Dimension - Bolt Size fraction	1/4
Length	0.62 in
Dimension - B Length fraction	5/8 in
Package Weight	0.000 lb.



Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	0.62 in
Width	0.25 in
Dimension - Thread Size	1/4 - 20
Dimension - Threads per inch	20
Dimension - Bolt Size inch	0.25 in

Force Related

Installation Torque	80 LBS/in
Recommended in-lb	

General

Trade Name	DURIMUM™
UPC	781810011270
Material	Silicon Bronze
UPC 12 Digit	781810011270
UPC 14 Digit GTIN	00781810011270

Logistics

Minimum Pack Quantity	1
Pallet Quantity	48000
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)