



264114T, Shear Bolt WEJTAP™ Connector, Small Series

By Burndy

Catalog # [264114T](#)



Main Conductor: 3/0 ACSR - 250 AAC (.502"-.574") Tap

Conductor: 2/0 ACSR - 3/0 (.447"-.502") Tin Plated

Features

- Industry-proven spring wedge technology easily installed with common socket or impact wrench
- Installed overhead
- Meets or exceeds current carrying capacity of conductors being connected
- "Spring like" high strength C-Body ensures permanent connection with consistent pressure on the conductors
- Corrosion resistant highly conductive copper and bronze alloys with a pure copper insert between conductors increases conductivity and lower electrical resistance
- Corrosion inhibitor factory applied for ease of installation
- Remains permanently locked through fault current or power surges
- Easy to remove without damage to conductor
- May be used in non-corrosive environments to connect copper conductors

- Excellent option for emergency restoration where outside crews might not have Shoot-On or compression tooling

General

Catalog Number	264114T
UPC	621945676848

Conductor Related

Conductor Range	Main Conductor: 3/0 ACSR-250 AAC, Tap: 2/0 ACSR-3/0
-----------------	---

Product Assets

[Excel Files - Burndy-CPI WEJTAP Connector Selector](#)

[Installation Manuals - Tap Connector Installation Instructions](#)

[Specifications - 264114T](#)

[Video - WEJTAP™ Installation with Gloves](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BDY-264114T-SPEC-EN | REV 7/2025