

264124T, Shear Bolt Stirrup Connector

By Burndy
Catalog # [264124T](#)



Conductor Range: 3/0 ACSR - 4/0 (.502"-.574") With 1/0 Tin Plated Bail (.313") Tin Plated

Features

- Industry-proven spring wedge technology easily installed with common socket or impact wrench
- Installed overhead
- Meets or exceeds current carrying capacity of conductors being connected
- "Spring like" high strength C-Body ensures permanent connection with consistent pressure on the conductors
- Corrosion resistant highly conductive copper and bronze alloys with a pure copper insert between conductors increases conductivity and lower electrical resistance
- Corrosion inhibitor factory applied for ease of installation
- Remains permanently locked through fault current or power surges
- Easy to remove without damage to conductor
- May be used in non-corrosive environments to connect copper conductors

- Excellent option for emergency restoration where outside crews might not have Shoot-On or compression tooling

General

Catalog Number	264124T
Type	Stirrups
UPC	621945677173

Conductor Related

Conductor Range	Main Conductor: 3/0 ACSR-4/0, 1/0 Bail
-----------------	--

Product Assets

[Installation Manuals - Hot-Stick Stirrup Installation Instructions](#)
[Specifications - 264124T](#)