



31X125HEBET, 5/16" x 1-1/4" Hex Bolt,
Silicon Bronze, Tin Plated

By Burndy
Catalog # 31X125HEBET

5/16 x 1.25 Electro Tin Plate Bolt



Features

- Tin Plated DURIMUM™ silicon bronze hardware combines high strength and corrosion resistance
- Silicon bronze per ASTM B99

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Bolt - Hex
----------------	------------

Dimensions

Dimension - Bolt Size fraction	5/16
Length	1.25 in
Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.25 in

Width	0.31 in
Dimension - Thread Size	5/16-18
Dimension - Threads per inch	18
Dimension - Bolt Size inch	0.3125 in

Force Related

Installation Torque	180 LBS/in
Recommended in-lb	

General

Trade Name	DURIMUM™
UPC	781810256114
Material	Silicon Bronze
UPC 12 Digit	781810256114
UPC 14 Digit GTIN	00781810256114

Logistics

Minimum Pack Quantity	500
Pallet Quantity	99999
Carton Quantity	500

Product Assets

[Catalog \[English\]](#)