



31X300HEBBOX, 5/16" x 3" Hex Bolt, Silicon Bronze

By Burndy
Catalog # [31X300HEBBOX](#)

Silicon Bronze Hexagonal Head Bolt, 3 IN L, 5/8 IN-11 Thread Size



Features

- DURIMUM™ silicon bronze hardware combines high strength and corrosion resistance
- Silicon bronze per ASTM B99

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Bolt - Hex
----------------	------------

Dimensions

Package Height	0.000 in
Dimension - Bolt Size fraction	5/16
Length	3 in
Dimension - B Length fraction	3 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	3 in
Width	0.31 in
Dimension - Thread Size	5/16-18
Dimension - Threads per inch	18
Dimension - Bolt Size inch	0.3125 in

Force Related

Installation Torque	180 LBS/in
Recommended in-lb	

General

Trade Name	DURIMUM™
UPC	781810011959
Material	Silicon Bronze
UPC 12 Digit	781810011959
UPC 14 Digit GTIN	00781810011959

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)