

## 364710, Shear Bolt Stirrup Connector

By Burndy  
Catalog # [364710](#)



Conductor Range: 350 MCM - 477 AAC (.681" - .795") with 2/0 Tin Plated Bail (.375")

### Features

- Industry-proven spring wedge technology easily installed with common socket or impact wrench - No Special Tools Required!
- "Spring Like" high strength C-Body ensures permanent connection with consistent pressure on the conductors
- Meets or exceeds current carrying capacity of conductors being connected
- Corrosion resistant highly conductive aluminum alloys with a pure aluminum insert between conductors increases conductivity and lowers electrical resistance
- Corrosion inhibitor factory applied for ease of installation
- Remains permanently locked through fault current or power surges
- Easy to remove without damage to conductor

- May be used in non-corrosive environments to connect copper conductors
- Excellent option for emergency storm restoration

### General

|                |              |
|----------------|--------------|
| Catalog Number | 364710       |
| Type           | Stirrups     |
| UPC            | 621945683419 |

### Conductor Related

|                 |                                             |
|-----------------|---------------------------------------------|
| Conductor Range | Main Conductor: 350 kcmil-477 AAC, 2/0 Bail |
|-----------------|---------------------------------------------|

### Product Assets

[Installation Manuals - Hot-Stick Stirrup Installation Instructions](#)  
[Specifications - 364710](#)