



38X125HGSB, 3/8" x 1-1/4" Hex Bolt, Galvanized Steel

By Burndy
Catalog # 38X125HGSB

3/8 x 1.25 Galvanized Steel Bolt



Features

- Galvanized steel hardware (bolts, nuts, flatwashers and internal tooth lockwashers) are manufactured per ASTM307 Grade A
- Nut surfaces and bolt heads have American Standard dimensions
- Galvanizing is per ASTM A153

Specifications

Certification - ETL	No
Standards - RoHS Compliance	NC
Status	
UL Listed	No
Certification - CSA Approved	No

Dimensions

Height	0.268 in
--------	----------

Width	0.38 in
Dimension - Bolt Size fraction	3/8
Length	1.25 in
Dimension - Thread Size	3/8-16
Dimension - Threads per inch	16
Dimension - B Length fraction	1-1/4 in
Dimension - Bolt Size inch	0.38 in
Dimension - Length Overall	1.25 in
inch	
Dimension - B Length inch	1.25 in
Dimensions	1.25 in x 0.38 in x 0.268 in

General

UPC	781810162514
Material	GALVANIZED STEEL

Product Assets

[Catalog \[English\]](#)