



38X125OSB, 3/8" x 1-1/4" Oval Shank Bolt



By Burndy
Catalog # [38X125OSB](#)

3/8 x 1.25 Oval Shank Bolt

Features

- Prevents Rotation
- Increased Stability
- Reduces wear and tear on the hole and bolt
- Improved load distribution and specified application fit

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Dimensions

Height	0.268 in
Width	0.38 in
Dimension - Bolt Size fraction	3/8
Length	1.25 in
Dimensions	1.25 in x 0.38 in x 0.268 in

General

UPC	781810259511
Material	SILICON BRONZE

Product Assets

[Catalog \[English\]](#)