



38X150HEBET, 3/8" x 1-1/2" Hex Bolt, Silicon Bronze, Tin Plated

By Burndy
Catalog # [38X150HEBET](#)

3/8 x 1.50 Electro Tin Plated Bolt



Features

- Tin Plated DURIUM™ silicon bronze hardware combines high strength and corrosion resistance
- Silicon bronze per ASTM B99

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Bolt - Hex
----------------	------------

Dimensions

Package Height	0.000 in
Dimension - Bolt Size fraction	3/8
Length	1.5 in
Dimension - B Length fraction	1-1/2 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - B Length inch	1.5 in
Height	0.268 in
Width	0.38 in
Dimension - Thread Size	3/8-16
Dimension - Threads per inch	16
Dimension - Bolt Size inch	0.375 in
Dimensions	1.5 in x 0.38 in x 0.268 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	

General

Trade Name	DURIUM™
UPC	781810158920
Material	SILICON BRONZE
UPC 12 Digit	781810158920
UPC 14 Digit GTIN	00781810158920

Logistics

Pallet Quantity	30000
Carton Quantity	500

Product Assets

[Catalog \[English\]](#)