



38X175HEBBOX, 3/8" x 1-3/4" Hex Bolt, Silicon Bronze

By Burndy
Catalog # 38X175HEBBOX

Silicon Bronze Hexagonal Head Bolt, 1.75 IN L, 3/8 IN-16 Thread
Size

Features

- DURIMUM™ silicon bronze hardware combines high strength and corrosion resistance
- Silicon bronze per ASTM B99

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Bolt - Hex
----------------	------------

Dimensions

Package Height	0.000 in
Dimension - Bolt Size fraction	3/8
Length	1.75 in
Dimension - B Length fraction	1-3/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in



Dimension - B Length inch	1.75 in
Height	0.268 in
Width	0.38 in
Dimension - Thread Size	3/8-16
Dimension - Threads per inch	16
Dimension - Bolt Size inch	0.375 in
Dimension - Length Overall inch	1.75 in
Dimensions	1.75 in x 0.38 in x 0.268 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	

General

Trade Name	DURIMUM™
UPC	781810011478
Material	Silicon Bronze
UPC 12 Digit	781810011478
UPC 14 Digit GTIN	00781810011478

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)