



38X175OSBBOX, 3/8" x 1-3/4" Oval Shank Bolt



By Burndy
Catalog # 38X175OSBBOX

3/8 x 1.75 Oval Shank Bolt

Features

- Prevents Rotation
- Increased Stability
- Reduces wear and tear on the hole and bolt
- Improved load distribution and specified application fit

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Bolt - Oval Shank
----------------	-------------------

Dimensions

Dimension - Bolt Size fraction	3/8
Length	1.75 in
Dimension - B Length fraction	1-3/4 in

Dimension - B Length inch	1.75 in
Height	0.268 in
Width	0.38 in
Dimension - Thread Size	3/8-16
Dimension - Threads per inch	16
Dimension - Bolt Size inch	0.375 in
Dimensions	1.75 in x 0.38 in x 0.268 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	

General

UPC	781810362037
Material	Silicon Bronze
UPC 12 Digit	781810362037
UPC 14 Digit GTIN	00781810362037

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)