



38X200HSSBUSA, 3/8" x 2" Hex Bolt, Stainless Steel

By Burndy
Catalog # [38X200HSSBUSA](#)

3/8 x 2.00 Stainless Steel Bolt



Features

- Stainless Steel hardware is manufactured from 18-8 non-magnetic material
- Nut surfaces and bolt heads have American National Coarse Series, Class #2 fit

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Bolt - Hex
----------------	------------

Dimensions

Package Height	0.000 in
Dimension - Bolt Size fraction	3/8
Length	2 in
Dimension - B Length fraction	2 in
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in
Dimension - B Length inch	2 in
Height	0.268 in
Width	0.38 in
Dimension - Thread Size	3/8-16
Dimension - Threads per inch	16
Dimension - Bolt Size inch	0.38 in
Dimensions	2 in x 0.38 in x 0.268 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	

General

UPC	781810330401
Material	Stainless Steel
UPC 12 Digit	781810330401
UPC 14 Digit GTIN	00781810330401

Logistics

Minimum Pack Quantity	1
Pallet Quantity	89100
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)