



38X225HEBET, 3/8" x 2-1/4" Hex Bolt, Silicon Bronze, Tin Plated

By Burndy
Catalog # [38X225HEBET](#)

3/8 x 2.25 Electro Tin Plated Bolt



Features

- Tin Plated DURIUM™ silicon bronze hardware combines high strength and corrosion resistance
- Silicon bronze per ASTM B99

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Bolt - Hex
----------------	------------

Dimensions

Package Height	0.000 in
Dimension - Bolt Size fraction	3/8
Length	2.25 in
Dimension - B Length fraction	2-1/4 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	2.25 in
Height	0.268 in
Width	0.38 in
Dimension - Thread Size	3/8-16
Dimension - Threads per inch	16
Dimension - Bolt Size inch	0.375 in
Dimensions	2.25 in x 0.38 in x 0.268 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	

General

Trade Name	DURIUM™
UPC	781810463093
Material	SILICON BRONZE
UPC 12 Digit	781810463093
UPC 14 Digit GTIN	00781810463093

Product Assets

[Catalog \[English\]](#)



A Hubbell brand