



50X125HEBET, 1/2" x 1-1/4" Hex Bolt, Silicon Bronze, Tin Plated

By Burndy
Catalog # 50X125HEBET

1/2 x 1.25 Electro Tin Plated Hex Bolt



Features

- Tin Plated DURIUM™ silicon bronze hardware combines high strength and corrosion resistance
- Silicon bronze per ASTM B99

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Bolt - Hex
----------------	------------

Dimensions

Package Height	0.000 in
Dimension - Bolt Size fraction	1/2
Length	1.25 in
Dimension - B Length fraction	1-1/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - B Length inch	1.25 in
Height	0.364 in
Width	0.5 in
Dimension - Thread Size	1/2-13
Dimension - Threads per inch	13
Dimension - Bolt Size inch	0.5 in
Dimensions	1.25 in x 0.5 in x 0.364 in

Force Related

Installation Torque	480 LBS/in
Recommended in-lb	

General

Trade Name	DURIUM™
UPC	781810109298
Material	Silicon Bronze
UPC 12 Digit	781810109298
UPC 14 Digit GTIN	00781810109298

Logistics

Minimum Pack Quantity	200
Pallet Quantity	14800
Carton Quantity	200

Product Assets

[Catalog \[English\]](#)